

**FAG****22215-E1-XL**

## Spherical Roller Bearing

Spherical roller bearings 222...-E1, main dimensions to DIN 635-2

**X-life**

## Technical information

**Your current product variant**

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

**Main Dimensions & Performance Data**

d	75 mm	Bore diameter
D	130 mm	Outside diameter
B	31 mm	Width
$C_r$	216,000 N	Basic dynamic load rating, radial
$C_{0r}$	237,000 N	Basic static load rating, radial
$C_{ur}$	30,500 N	Fatigue load limit, radial
$n_G$	6,500 1/min	Limiting speed
$n_{gr}$	3,700 1/min	Reference speed
$\approx m$	1.668 kg	Weight

**Mounting dimensions**

$d_{a \min}$	84 mm	Minimum diameter shaft shoulder
$D_{a \max}$	121 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1.5 mm	Maximum recess radius



## Dimensions

$r_{\min}$	1.5 mm	Minimum chamfer dimension
$D_1$	117.7 mm	Bore diameter outer ring
$d_2$	89.8 mm	Raceway diameter of the inner ring
$d_s$	3.2 mm	Diameter lubrication hole
$n_s$	6.5 mm	Width of lubricating groove

## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

## Calculation factors

$e$	0.22	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y_1$	3.1	Dynamic axial load factor
$Y_2$	4.62	Dynamic axial load factor
$Y_0$	3.03	Static axial load factor

## Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment